# **Portable UVC Sterilization Light**



# **Appearance**







### **Parameter**

Model: USL-3W

Name: Portable UVC Sterilization Light

Material: ABS

External inferface: 1 USB port Product Size: 50x50x100 MM

Box Size: 55x55x105 MM

Watt: 2.5W


Voltage: DC 5V

Battery Capacity: 800mAh

Sterilization Area: 2 sq.m.

Working Temps: 0-40°C

Working Humidity: 10%-90%



### **Instructions**







- 1: Startup: After pressing and holding the switch button for 3 seconds, the backlight of switch button flashes. After 30 seconds, the UVC sterilization light lights up to start sterilization. The light automatically shuts down after 15 minutes of sterilization
- 2: Shutdown: Press the switch button lightly, the backlight of the switch button goes out or the UVC sterilization light goes out, and the sterilization can be stopped.









## Wardrobe







# Thank You!